

- **Material:** stainless steel
- **Color:** silver

The foot is protected by vulcanized rubber, complying with strict hygiene regulations.

The mentioned static load is calculated at the center of the screw. These values are reduced in the event of vibrations or dynamic loads.

This system is developed for use in dairies, pharmaceutical and food industries, and factories that are subject to the strictest hygiene regulations.

The housing is equipped with a seal that, by its adhesion to the smooth surface of the screw, ensures that dirt does not enter.

USDA ORGANIC Certificate

USDA Organic is the American national form of certification awarded according to criteria for organic agriculture.

The goal of this federal organization is to support trade, agricultural organic production and rural communities, protect the environment and ensure food safety.

Selected variant

Product name	Adjustable foot for clean rooms with anchoring bracket, vulcanized stainless steel
Product code	14228
Stroke adjustment (mm)	65
Height B (mm)	200
Foot diameter D (mm)	80
Height H2 (mm)	173
Diameter D1 (mm)	30
Static load (N)	10000
Height A (mm)	38
Thread F	M20
SW key	17
Height H1 (mm)	238
Pitch I (mm)	54
Foot height G (mm)	25

Variants

A components s.r.o.

Bohunická 493/81

619 00 Brno

Web: www.acomponents.cz

E-mail: info@acomponents.cz

Telefon: 511 188 963

Maloobchodní prodej

Standardizované komponenty můžete objednávat také v našem e-shopu.

Skladové zboží expedujeme obvykle do 48 hodin od potvrzení objednávky.

Product name	Product code	QTY	Stroke adjustment (mm)	Height B (mm)	Foot diameter D (mm)	Height H2 (mm)	Diameter D1 (mm)	Static load (N)	Height A (mm)	Thread F	SW key	Height H1 (mm)	Pit I (mm)
Parallel plugs Type 1, LDPE, natural	14222	0	40	125	60	95	24	7000	35	M16	17	160	45
Adjustable foot for clean rooms with anchoring bracket, vulcanized stainless steel	14223	0	65	150	60	120	24	7000	35	M16	17	185	45
Adjustable cleanroom foot with anchoring bracket, vulcan. stainless steel	14224	0	65	150	60	120	30	7000	35	M20	17	185	45
Adjustable cleanroom foot with anchoring bracket, vulcan. stainless steel	14225	0	40	125	80	98	24	10000	38	M16	17	163	54
Adjustable foot for clean rooms with anchoring bracket, vulcan. stainless steel	14226	0	65	150	80	123	24	10000	38	M16	17	188	54

Product name	Product code	QTY	Stroke adjustment (mm)	Height B (mm)	Foot diameter D (mm)	Height H2 (mm)	Diameter D1 (mm)	Static load (N)	Height A (mm)	Thread F	SW key	Height H1 (mm)	Pit I (mm)
Adjustable foot for clean rooms with anchoring bracket, vulcan. stainless steel	14227	10	65	150	80	123	30	10000	38	M20	17	188	54
Adjustable foot for clean rooms with anchoring bracket, vulcanized stainless steel	14228	0	65	200	80	173	30	10000	38	M20	17	238	54
Adjustable foot for clean rooms with anchoring bracket, vulcanized stainless steel	14229	0	65	150	100	128	24	15000	43	M16	17	193	69
Adjustable cleanroom foot with anchoring bracket, vulcan. stainless steel	14230	0	65	150	100	128	30	15000	43	M20	17	193	69

Product name	Product code	QTY	Stroke adjustment (mm)	Height B (mm)	Foot diameter D (mm)	Height H2 (mm)	Diameter D1 (mm)	Static load (N)	Height A (mm)	Thread F	SW key	Height H1 (mm)	Pit I (mm)
Adjustable foot for clean rooms with anchoring bracket, vulcanized stainless steel	14231	0	65	150	100	129	35	15000	44	M24	20	194	69
Adjustable cleanroom leg with anchoring bracket, vulcanized stainless steel	14232	0	65	150	100	130	42	15000	45	M30	26	195	69
Adjustable cleanroom foot with anchoring bracket, vulcan. stainless steel	14233	0	65	200	100	178	30	15000	43	M20	17	243	69
Adjustable leg for clean rooms with anchoring bracket, vulcan. stainless steel	14234	0	65	200	100	179	35	15000	44	M24	20	244	69

Product name	Product code	QTY	Stroke adjustment (mm)	Height B (mm)	Foot diameter D (mm)	Height H2 (mm)	Diameter D1 (mm)	Static load (N)	Height A (mm)	Thread F	SW key	Height H1 (mm)	Pit I (mm)
Adjustable cleanroom foot with anchoring bracket, vulcanized stainless steel	14235	0	65	200	100	180	42	15000	45	M30	26	245	69

A components s.r.o.

Bohunická 493/81

619 00 Brno

 Web: www.acomponents.cz

 E-mail: info@acomponents.cz

Telefon: 511 188 963

Maloobchodní prodej

Standardizované komponenty můžete objednávat také v našem e-shopu.

Skladové zboží expedujeme obvykle do 48 hodin od potvrzení objednávky.