

- **Material:** stainless steel
- **Color:** silver

The foot has a protective gray EPDM rubber seal, which complies with strict hygiene regulations.

The static load mentioned is calculated on the center of the screw. In the case of vibrations or dynamic loads, these values are lower.

This system is developed for use in dairies, pharmaceutical and food industries, and factories that are subject to the strictest hygiene regulations.

The housing is equipped with a seal that, by its adhesion to the smooth surface of the screw, ensures that dirt does not enter.

## Selected variant

<b>Product name</b>	Adjustable foot for clean operations with vulcanized foot, stainless steel
<b>Product code</b>	28240
<b>Thread F</b>	M20
<b>Height H1 (mm)</b>	185
<b>Stroke adjustment (mm)</b>	65
<b>Height H2 (mm)</b>	121
<b>Foot diameter D (mm)</b>	60
<b>Weight (g)</b>	655
<b>Height A (mm)</b>	35
<b>Foot height G (mm)</b>	22
<b>Static load (N)</b>	7000
<b>SW key</b>	17/26
<b>Diameter D1 (mm)</b>	30
<b>Height B (mm)</b>	150

## Variants

Product name	Product code	QTY	Thread F	Height H1 (mm)	Stroke adjustment (mm)	Height H2 (mm)	Foot diameter D (mm)	Weight (g)	Height A (mm)	Foot height G (mm)	Static load (N)	SW key	D
--------------	--------------	-----	----------	----------------	------------------------	----------------	----------------------	------------	---------------	--------------------	-----------------	--------	---

Adjustable foot for clean operations with vulcan. foot, stainless steel	28239	6	M16	160	40	95	60	412	35	22	7000	17/20	24
Adjustable foot for clean operations with vulcanized foot, stainless steel	28240	0	M20	185	65	121	60	655	35	22	7000	17/26	30
Adjustable leg for clean operations with vulcan. foot, stainless steel	28242	0	M16	188	65	123	80	527	38	25	10000	17/20	24
Adjustable foot for clean operations with vulcan. foot, stainless steel	28241	0	M16	163	40	98	80	494	38	25	10000	17/20	24
Adjustable foot for clean operations with vulcan. foot, stainless steel	28245	0	M16	191	65	128	100	691	41	28	15000	17/20	24

Adjustable foot for cleanrooms with vulcanized foot, stainless steel	28244	0	M20	238	65	173	80	839	38	25	10000	17/26	30
Adjustable foot for clean operations with vulcanized foot, stainless steel	28243	0	M20	188	65	123	80	737	38	25	10000	17/26	30
Adjustable foot for clean operations with vulcan. foot, stainless steel	28248	0	M30	195	65	130	100	1467	43	28	15000	26/36	42
Adjustable foot for clean operations with vulcan. foot, stainless steel	28246	0	M20	191	65	128	100	901	41	28	15000	17/26	30
Nastavitelná noha pre čisté prevádzky s vulkan. pätkou, nerez	28247	0	M24	192	65	129	100	1092	42	28	15000	20/30	35

Adjustable foot for cleanrooms with vulcanized foot, stainless steel	28249	0	M20	241	65	176	100	1003	41	28	15000	17/26	30
Adjustable foot for clean operations with vulcan. foot, stainless steel	28251	0	M30	245	65	180	100	1692	43	28	15000	26/36	42
Adjustable foot for clean operations with vulcan. foot, stainless steel	28252	0	M16	195	65	130	120	1040	-	32	30000	17/20	-
Adjustable foot for clean operations with vulcan. foot, stainless steel	28250	0	M24	242	65	179	100	1239	42	28	15000	20/30	35
Adjustable foot for cleanrooms with vulcanized foot, stainless steel	28255	0	M30	199	65	134	120	1816	-	32	30000	26/36	-

Adjustable foot for clean operations with vulcan. foot, stainless steel	28253	0	M20	195	65	130	120	1250	-	32	30000	17/26	-
Adjustable foot for clean operations with vulcan. foot, stainless steel	28254	0	M24	196	65	131	120	1441	-	32	30000	20/30	-
Adjustable foot for clean operations with vulcan. foot, stainless steel	28258	0	M30	249	65	184	120	2041	-	32	30000	26/36	-
Adjustable foot for clean operations with vulcan. foot, stainless steel	28256	0	M20	245	65	180	120	1352	-	32	30000	17/26	-
Adjustable foot for cleanrooms with vulcanised foot, stainless steel	28257	0	M24	246	65	181	120	1588	-	32	30000	20/30	-

Adjustable foot for clean operations with vulcan. foot, stainless steel	27524	13	M16	185	65	120	60	445	35	22	7000	17/20	24
---	-------	----	-----	-----	----	-----	----	-----	----	----	------	-------	----

**A components s.r.o.**

Bohunická 493/81  
619 00 Brno

Web: [www.acomponents.cz](http://www.acomponents.cz)  
E-mail: [info@acomponents.cz](mailto:info@acomponents.cz)  
Telefon: 511 188 963

**Maloobchodní prodej**

Standardizované komponenty můžete objednávat také v našem e-shopu.

Skladové zboží expedujeme obvykle do 48 hodin od potvrzení objednávky.